

Standard and High Density D-sub Arrangements

Shell Size	Standard Density # of contacts	High Density # of contacts
1 (E)	9	15
2 (A)	15	26
3 (B)	25	44
4 (C)	37	62
5 (D)	50*	78

Standard density uses a size 20 contact.

High Density uses a smaller size 22 contact in a 3 row configuration.

Shell sizes are the same overall dimensions.

* 50 POSITION STANDARD DENSITY IS 3 ROW

Shell Size 2
 15 position Standard
 2 row pictured



Shell Size 2
 26 position High Density
 3 row pictured

